




DH-T63217XD



DH-B63220UXD



DH-B63217XD



Feature

- Full HD 1080p HDMI camera
- High sensitivity!
- High performance.
- Full HD image pixel

UNIT:±0.5mm

Specification

Model	DH-T63217HD	DH-T63217FD	DH-B63217HD	DH-B63217FD	DH-B63220UHD	DH-B63220UFD
Max. frame rate	HD 1280 x 720 @30 fps	FHD 1920 x 1080 @30 fps	HD 1280 x 720 @30 fps	FHD 1920 x 1080 @30 fps	HD 1280 x 720 @30 fps	FHD 1920 x 1080 @30 fps
pixel size	4.2umx4.2um					
Image sensor	1/2.9" digital 1080p CMOS camera					
Image area	5.51 x 3.1mm					
Scan mode	progressive					
Sensitivity	7.0 V/lux.sec					
Dynamic range	55.1 dB					
SNR Range	39.8 dB					
Storage temperature	-40 to 150 Degree C					
Working temperature	-10 to 105 Degree C					
Interface	HDMI D type					
Power source	DC 5~12V					
Power current	5V/350mA(Min.) 12V/150mA(Min.)	5V/430mA(Min.) 12V/180mA(Min.)	5V/350mA(Min.) 12V/150mA(Min.)	5V/430mA(Min.) 12V/180mA(Min.)	5V/350mA(Min.) 12V/150mA(Min.)	5V/430mA(Min.) 12V/180mA(Min.)
Dimension(mm)	Ø 18.5mmx60.8mm		Ø 17.4mmx40mm		20mmx50.5mm	

Order information

Model	Lens	Type
DH-T63217XD	N/A	Tube camera
DH-B63217XD	N/A	camera module
DH-B63220UXD	N/A	camera module

MISUMI offers different lenses to match with HDMI camera.

