



Feature

- Plug and Play (Driver Free)
- HDMI 720P Video & Audio input
- 360 Degree view angle

Specification

Unit : mm (± 0.5)

Model	MD-VC100M
Image Sensor	1/4" HD 720P CMOS Camera
Number Of Effective Pixels	1280x720 MJPEG
Video format	MJPEG
Frame rate	30 fps for 1280x720 MJPEG
USB Interface	USB 2.0 Full Speed
USB Driver	Standard UVC1.1/UAC1.0
Video	Sensor Image
Audio	Support D-mic
Max. Working Current	1.063A@5V
Working temperature	0°C~ 70°C
Built-in Lens	180 degree lens x 2
Power Consumption	5315mW
OS support	Windows XP SP2, Windows 7, Windows VISTA, Windows 8 and MAC OSX series.
Dimension(mm)	140x58x49.3

- Plug and play into the USB port of NB, Laptop and Desktop PC, etc.
- This camera is driver free(UVC 1.1 version and UAC 1.0)
- Software supprot: AMCAP, KMPLAYER, SKYPE, MANYCAM, etc.

