



Unit: mm

## Specification

Model	L09520IR-M7	L09520AR-M7
Sensor type	1/3"	
Field Angle (D/H/V)	138.0° / 117.0° / 96.4°	
Filter type	IR 650nm	AR
EFL (mm)	0.95mm	
Aperture F/no	2.0	
IRIS	Fixed	
Lens Construction	4G1P + IRF (6E)	
Mount	M7.0 x P0.35	
Diameter of lens (mm)	$\phi 10.0 \times 7.63$	
TV distortion	< -25%	
Image Height	$\phi 5.0\text{mm}$	

\*NO Lens holder