



Unit: mm

Specification

Model	LP2525IRC-M10
Sensor type	1/3"
Field Angle (D)	125°
Filter type	IR cut 650nm
EFL (mm)	2.5mm
Aperture F/no	2.5
Iris	Fixed
Total track	TTL 11.5
Mount	M10 x P0.5
Diameter of lens (mm)	$\phi 10 \times 8.7$
Lens Construction	4C/5E (All Glass)

*NO Lens holder