



Unit: mm

### Specification

Model	13M42024IR-M6.5
Sensing area	1/3.2"
Sensor size	Ø6.0mm
Focal length	4.2mm
Back focal length	1.0 mm
Optional distortion	< -1.0%
F/NO	2.4
Field of view(D)	70°
Resolution	13MP
M.O.D	>30mm
Lens construction	5P+IR
Thread sized	M6.5 x P0.25