



Unit: mm

Specification

Model	1M10028ARV-M12
Sensing area	1/3"
Focal length	10±5%
Back focal length	5.3±5% mm (in air)
Flange back length	4.3±5% mm
F/NO	2.8±5%
Iris	Fixed
Field of view(D/H/V)	35° / 28° / 21°
Resolution	1.3MP
M.O.D	0.3m
Lens construction	4 components 4 element
Thread sized	M12 x P0.35-6g