



Unit: mm

Specification

Model	1M15025ARV-M12
Sensing area	1/2"
Focal length	15 mm
Back focal length	12 mm
Flange back length	5 mm
F/NO	2.5 \pm 5%
Field of view(D)	30°
Resolution	1.3MP
M.O.D	0.3m
Thread sized	M12 x P0.5-6g