



Unit: mm

Specification

Model	1M33024IR-M7	
Sensor type	1/3"	1/4"
Field Angle (D/H/V)	130° / 77° / 55.1°	72.7° / 55.1° / 39.1°
Filter type	IR	
EFL (mm)	3.30mm	
Aperture F/no	2.4	
Pixel	1.3MP	
Lens Construction	5G	
Mount	M7.0 x P0.5	
Diameter of lens (mm)	ø 7.0 x 9.56	
TV distortion	-66.40%	-22.80%

*NO Lens holder