



Unit: mm

Specification

Model	1M80025IRV-M7
Sensing area	1/3"
Focal length	8±5%
Back focal length	5.8mm (in air)
Flange back length	2.84mm
F/NO	2.5±5%
Iris	Fixed
Field of view(D/H/V)	45° / 36.5° / 27.5°
Resolution	1.3MP
M.O.D	30cm
Lens construction	4 components 4 element
Thread sized	M7 x P0.5-6g