



Unit: mm

Specification

Model	2M45016AR-M12
Sensing area	1/3"
Focal length	45 mm
Back focal length	5.5 mm
Iris	fixed
F/NO	2.5±5%
Field of view(D)	6.8°
Resolution	2MP
M.O.D	0.2m
Thread sized	M12 x P0.5-6.5g