



Unit: mm

### Specification

Model	3M36520IR-M7
Image circle(mm)	(D)7.8
Focal length	3.65 mm
F/NO.	2.0
Back focal length	2.8 mm
TTL	15.95 mm
Field of view(D/H/V)	120°/96.5°/52.2°(1/2.7")
Construction	6G + IR
Thread sized	M7 x P0.35