



Unit: mm

Specification

Model	5M1675AR-M12
Sensor type	1/4"
Field Angle (D/H/V)	1/2": 28.5°/22.8°/17.7° 1/3": 21.5°/17.2°/12.9° 1/4": 16.2°/13°/9.7°
Image format	1/2"
EFL (mm)	16mm
Aperture F/no	2.0
MBF	6.3 mm
Mount	M12 x P0.5
Back focal length	7.1mm

*NO Lens holder