



Unit: mm

## Specification

Model	L12920IR-M12
Sensor type	1/2.9"
Filter type	IR
Max image circle	Ø5.8 mm
BFL (mm)	1.98±0.1mm
TTL	15.11±0.2mm(at INF)
FNO	2.0
Field of view	113°(V), 190°(H), 205°(D)
Chief ray angle	<21.2°
IR-Cut Filter	T50%=650±10nm
Barrel thread	M12 x P0.5