



Unit: mm

## Specification

Model	L2110LIR-M5.5-52	L2125L9AR-M5.5-52	L2125L8AR-M5.5-52
LED	white LED x 6	IR 940nm LED x 6	IR 850nm LED x 6
EFL (mm)	2.1mm		
Aperture F/no	10±5%	2.5±5%	2.5±5%
Filter type	IR	AR	AR
Sensor type	1/4"		
Field Angle	1/4" : 72°(V) / 96°(H) / 125°(D)		
Back Focal Length	2.395mm (Tol: ±0.4mm, in air)		
Lens Construction	2P 3G		
Mount	M5.5 x P0.35		
Iris	Fixed		

\*NO Lens holder