



Unit: mm

Specification

| Model | LP63844IR-M7 | LP63844AR-M7 |
|---------------------|-----------------------|--------------|
| Filter type | IR | AR |
| Sensor type | 1/3" | |
| Field Angle (D/H/V) | 60.4° / 50.6° / 37.4° | |
| EFL (mm) | 6.38mm | |
| Aperture F/no | 4.4 | |
| Image Circle(Max) | ø 7.74mm | |
| Lens Construction | 2G | |
| Mount | M7.0 x P0.5 | |
| TV Distortion | <6.7% | |
| Chief ray angle | <21.5° | |

*NO Lens holder