



Unit: mm

Specification

Model	LP8324IR-M7	LP8324AR-M7
Filter type	IR	AR
Sensor type	1/4"	
Field Angle (D/H/V)	31° / 24.8° / 18.6°	
EFL (mm)	8.3mm	
Aperture F/no	2.4	
Image Circle(Max)	ø 4.5mm	
Lens Construction	4Component 4Element	
Mount	M7.0 x P0.5	
TV Distortion	-0.65%	
TTL	13.43 mm±5%	

*NO Lens holder