



Specification

Features:	Connects to Windows XP machines USB 2.0 port
	TCP Video MJPEG stream 1280 x 720 /YUV 10fps/ MJPEG 30fps/ H.264 24fps 640 x 480 /30 fps 320 x 200 /30 fps
	Driver free (USB Video Class) for any OS (windows XP, windows 7, windows 8, windows 10, MAC OS)
Model	MD-N41XX
Number of effective pixels	1280 x 720 /YUV 10fps/ MJPEG 30fps/H.264 24fps 640 x 480 /30 fps; 640 x 360 /30 fps 320 x 240 /30 fps; 320 x 180 /30 fps
pixel size	3 umx3 um
Image sensor	1/4" WXGA HD 720P Camera
Image area	3888 um x 2430 um
S/N Ratio	39 dB
Scan mode	progressive
Sensitivity	3300mV/(Lux)
Dark Current	20 mV/Sec
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Audio Output	20-16000Hz,S/N more than 58dB
Built-in Lens	4.0mm /F2.0
Power source	DC 5V
Power current	150 mA
Dimension(mm)	40.7 x 10.3mm
Audio	Built-in microphone

With special clip,
camera stays tight even
when running and jumping.



Slim Size is perfect for wearable and hidden!



Order Information

MODEL	OUTPUT
MD-N41XX	USB 2.0 A type
MM-N41XX	Micro USB OTG B type
MT-N41XX	USB Type-C
MX-N4131S	S:straight cable(150cm)
MX-N4131Q	