
Image	Model	Dimension (mm)	Power Input	Power output	Power Current	Note
	VT-0528S	2 (W) x 8 (L)	DC 2.9 ~5V	DC 2.8V	150 mA	-
	VT-0533R	6.8 (D)	DC 5V	DC 3.3V	150 mA	-
	VT-0533S	2 (W) x 8 (L)	DC 3.4 ~5V	DC 3.3V	150 mA	-
	VT-0533S-01	2 (W) x 2 (L)	DC 5V	DC 3.3V	400 mA	-
	VT-0512P-300	300 (Cable length)	DC 5V	DC 12V	300 mA	Iris 4 pin female for camera to Iris 4 pin male *switching power board
	VT-1202833	7 (W) x 37 (L)	DC 5~ 12V	DC 3.3V DC 2.8V	200 mA 150 mA	with ON/OFF switch. *switching power board
	VT-12033	8 (W) x 20 (L)	DC 4~12V	DC 3.3V	200 mA	*switching power board
	VT-12033-01	13 (D)	DC 4.5~12V	DC 3.3V	300 mA	*switching power board
	VT-12033-04	8 (W) x 10 (L)	DC 5~ 12V	DC 3.3V	100 mA	-
	VT-12033X-01	7 (W) x 24 (L)	DC 5~12 V	DC 3.3V	500 mA	*switching power board
	VT-1202V	8 (W) x 20 (L)	DC 3.6~12V	DC 2.8V	200 mA	Adjustable Voltage *switching power board

Image	Model	Dimension (mm)	Power Input	Power output	Power Current	Note
	VT-1204V	8 (W) x 20 (L)	DC 5.3~12V	DC 2.8V~4.2V	200 mA	Adjustable Voltage *switching power board
	VT-1205	8 (W) x 20 (L)	DC 12V	DC 5V	300 mA	*switching power board
	VT-1205-04	8 (W) x 10 (L)	DC 7~ 12V	DC 5V	200 mA	-
	VT-1205Y-USB	300 (Cable length)	DC 12V	DC 12V (DC plug 5.5/2.1mm) DC 5V (mini USB type B)	900 mA	-
	VT-24035	8 (W) x 22 (L)	DC 24V	DC 3.5V	-	*switching power board
	VT-2412	8 (W) x 22 (L)	DC 24V	DC 12V	-	*switching power board
	VT-LDM01	13 (W) x 26 (L)	DC 5V	DC 3.5V	-	-
	VT-0533-01	3.7 (W) x 12 (L)	DC 5V	DC 3.3V	150 mA	
	VT-05012	4 (W) x 5 (L)	DC 5V	DC 1.2V	400 mA	
	VT-05033	4 (W) x 5 (L)	DC 5V	DC 3.3V	400 mA	
	VT-05033-01	5 (W) x 6.8 (L)	DC 5V	DC 3.3V	400 mA	*switching power board