
MISUMI
Manufacturer & Exporter
TEL: 886-2-2226-6303
FAX: 886-2-2222-5620
mscctv@misumi.com.tw
http://www.misumi.com.tw

CCIQ II COLOR CAMERA

Body Type




UNIT: ±0.5mm

Feature

- Micro USB OTG B type
  Plug & Play!
- Comfortable to wear,
  Light weight 55g
- Application Possibility:
  Earthquake debris, tornado, hurricane, flood, avalanche, Law enforcement, so on..

Specification

Model	MX-102	MX-112
Video fomat	YUV / MJPEG	YUV / MJPEG / H.264
Number of effective pixels	1280 x 720 /YUV 10fps/ MJPEG 30fps 640 x 480 /30 fps 320 x 200 /30 fps	1280 x 720 /YUV 10fps/ MJPEG 30fps/ H.264 24fps 640 x 480 /30 fps 320 x 200 /30 fps
pixel size	3 um x 3 um	
Image sensor	1/4" WXGA HD 720P Camera	
Image area	3888 um x 2430 um	
S/N ratio	39 dB	
Scan mode	progressive	
Sensitivity	3300mV/(Lux)	
Dark current	20 mV/Sec	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Built-in lens	3.4mm /F2.8	
LED	N/A- Optional	
Power source	DC 5V	
Power current	150 mA	
Operating system support	Driver free (USB Video Class) for any OS (windows XP Linux any version, MAC OS)	



Model Information

Model	Connector
MM-102	Micro USB OTG B type
MT-102	USB C type
MD-102	USB 2.0 A type
MI-102	Mini USB B type
MM-112	Micro USB OTG B type
MT-112	USB C type
MD-112	USB 2.0 A type
MI-112	Mini USB B type