
Feature


- Competitive Price and outstanding quality!
- High Performance with compact size.
- Backlight Compensation.
- Built-In Microphone.

ST-101A
3.7 mm / F 2.0 (62°) / with OSD Function






ST-3501A
4.3 mm / F 2.0 (55°)





Ordering Information



Unit: ± 0.5 mm

Specification

Model		ST-101A	ST-3501A
Image Sensor		1/4" Color CCD	1/4" Color CCIQ II
Video System		NTSC / PAL	
Effective Pixels	NTSC	768 (H) × 494 (V)	648 (H) × 488 (V)
	PAL	752 (H) × 582 (V)	
Resolution (TV Lines)		520	400
S/N Ratio		More Than 48dB	More Than 50dB
Illumination (Min.)		0.2 / F 1.2	0.1 / F 1.2
Lens		3.7 mm / F 2.0	4.3 mm / F 2.0
Shutter Speed		1/50-1/100,000 Sec.	TBD
Image Transfer Rate		TBD	60 fps
OSD Function		Support	N/A
Horizontal Sync Frequency		15.734 kHz (NTSC) 15.625 kHz (PAL)	
Vertical Sync Frequency		60 Hz (NTSC) 50 Hz (PAL)	
Camera Consumption		0.45	
Sensor Scan Mode		Progressive Scan	
Video Output		1Vp-p , 75ohm composite	
Audio Output		Built-In Microphone 20-16000 Hz, S/N more than 58dB	
Storage Temperature		-30 to 60 Degree C	
Working Temperature		-10 to 45 Degree C	
Power Source		DC 5~12V (Standard)	
Power Current		80 mA	

ST-101A

SERIES	CAMERA BODY	MICROPHONE
ST Headset	101 Color (with OSD Function) 3501 Color	A Built-In N/A None

Connector Information

