


## Specification

CMOS SNAKE CAMERA					
Model	MO-L806	MO-L575	MO-S575	MO-L1675	MO-S1675
Video system	NTSC / PAL		NTSC Only	NTSC / PAL	
Number of effective pixels	NTSC(EIA)	306 x 240	510 x 492	510 x 492	
	PAL(CCIR)	366 x 288	/	628 x 582	
Image sensor	1/5"PAL / 1/6"NTSC		1/4" Color	1/3" Color	
Resolution(TV Lines)	240		380		
S/N Ratio	more than 48dB				
AGC control	more than +27dB				
Minimum illumination	2 LUX	1.5 LUX		1 LUX	
Electronic shutter	1/50 - 1/57,000	1/50 - 1/63,000		1/50 - 1/125,000	
Horizontal sync frequency	NTSC(EIA)-15.734kHz / PAL(CCIR)-15.625kHz				
Vertical sync frequency	NTSC(EIA)-60Hz / PAL(CCIR)-50Hz				
Camera consumption	0.45				
Video output	1Vp-p , 75ohm composite				
Audio output	Frequency 20-16,000Hz , S/N ratio more than 58 SPL(at 1000Hz)(Ordering in advance)				
Built-in lens	2.8 mm / F2.0	4.0 mm / F2.0			
Lens angle	2.8 mm / 60 Degree	4.0 mm / 64 Degree		4.0 mm / 80 Degree	
Power source	DC 9 -12V(Standard)				
Power current	35 mA			100 mA	
Dimension (mm)	9.2 x 14 (mm)	12 x 25 (mm)	12 x 23 (mm)	15 x 41.5 (mm)	

## Snake Cmos Camera

MO-L806	MO-L575	MO-S575	MO-L1675 , MO-S1675
<p>28</p> <p>9.2</p> <p>(With LED Light)</p>	<p>25</p> <p>12</p> <p>(With LED Light)</p>	<p>23</p> <p>12</p>	<p>41.2</p> <p>15</p> <p>(With LED Light - MO-L1675)</p>

75 ~ 3000 cm (order in advance)



## Feature

Snake camera with LED light

75cm flexible cable (flexible iron pipe protect)

Waterproof (IP-67)