



**Specification**

Features:	<ul style="list-style-type: none"> <li>• Connects to Windows XP machines USB 2.0 port</li> <li>• TCP Video MJPEG stream            1280 x 720 /YUV 10fps/ MJPEG 30fps/ H.264 24fps            640 x 480 /30 fps            320 x 200 /30 fps</li> <li>• Driver free (USB Video Class) for any OS (windows XP, windows 7, windows 8, windows 10, any version, MAC OS )</li> </ul>	
Model	MD-B40XX	MD-B41XX
Number of effective pixels	<ul style="list-style-type: none"> <li>• 1280 x 720 /YUV 10fps/ MJPEG 30fps</li> <li>• 640 x 480 /30 fps</li> <li>• 320 x 200 /30 fps</li> </ul>	<ul style="list-style-type: none"> <li>• 1280 x 720 /YUV 10fps/ MJPEG 30fps/ H.264 24fps</li> <li>• 640 x 480 /30 fps</li> <li>• 320 x 200 /30 fps</li> </ul>
pixel size	3 umx3 um	
Image sensor	1/4" WXGA HD 720P Camera	
Image area	3888 um x 2430 um	
S/N Ratio	39 dB	
Scan mode	progressive	
Sensitivity	3300mV/(Lux)	
Dark Current	20 mV/Sec	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Audio Output	20-16000Hz,S/N more than 58dB	
Built-in Lens	4.0mm /F2.0	
Power source	DC 5V	
Power current	150 mA	
Dimension(mm)	40.7 x 10.3mm	
Audio	Built-in microphone	

With special clip, camera stays tight even when running and jumping.



Slim Size is perfect for wearable and hidden!



**Order Information**

MODEL	OUTPUT
MD-N40XX	USB 2.0 A type
MM-N40XX	Micro USB OTG B type
MT-N40XX	USB Type-C