




Model: BL17204
Side view / Board type




Model: B17204
Front view / Board type



Model: T17204
Front view / Tube type + LED





Model: MD-L17204-65
Front view (Snake Camera)



Unit : ± 0.5 mm

Specification

Model	BL17204	B17204	T17204L
Dimensions (mm)	4 × 18	Ø 4 × 14.4	Ø 4.5 × 27
Orientation	Side View	Front View	Front View
LED	N/A	N/A	White LED × 6
Pixel Size (µm)	2.125 × 2.125 µm		
Active Image Size (mm)	1.37(H) × 1.04(V) × 1.72(D)		
Resolution	640 × 480 @ 30fps MJPG, YUV 320 × 240 @ 30fps MJPG, YUV		
Image Sensor	1/10" CMOS color		
Lens	Specify when ordering		
Sensor Scan Mode	Progressive		
Video Format	MJPG, YUV		
Storage Temperature	-30 to 60 Degree C		
Working Temperature	-10 to 45 Degree C		
Power Source	DC 5V		
Power Current	130 mA (max)		
OS support	Windows XP, Windows Vista, Window 7, Windows 8, windows 10		



MD-B17204L-65



SERIES	CONNECTOR	CAMERA TYPE	DISPLAY	LED	LENS
M Basic	D USB 2.0 Type C M Micro USB OTG Type B T USB 2.0 Type C I Mini USB Type B	Front View B Board Type VB Board Type + Dimmer T Tube Type V Tube Type + Dimmer Side View BL Board Type	17204 Color 172M4 B / W	L White LED	65 1.33mm / F2.0 (65") 59 1.498mm / F3.2 (59") 59 1.498mm/F5.0 (59") 113 1.0mm / F4.8 (113")