



Unit: mm

Specification

Model	2M38028IRF-M7
Sensor type	1/4"
Field Angle (D)	66°
Image circle	4.8 mm
EFL (mm)	3.8mm
Aperture F/no	2.8
Total Track	3.75
Lens Construction	3P+ IR filter
Mount	M7 x P0.35
Chief Ray Angle	<math>< 15^\circ</math>
Back focal length	1.0mm

*NO Lens holder