



Unit: mm

### Specification

Model	2M70016IR-M12
Sensing area	1/3"
Focal length	70.0 mm
Back focal length	5.5 mm
Iris	fixed
F/NO	1.6
Field of view(D)	3.98°
Resolution	2MP
M.O.D	0.2m
Thread sized	M12 x P0.5-16g