



Unit: mm

Specification

Model	3M45028IRF-M7	3M45028ARF-M7
Filter type	IR	AR
Sensor type	1/3"	
Field Angle (D)	68°	
EFL (mm)	4.5mm	
Aperture F/no	2.8	
Pixel	3MP	
Chief ray angle	<15°	
Mount	M7 x P0.35	
Diameter of lens (mm)	ø7 x 9.56	
TV distortion	-1.5%	

*NO Lens holder