

Specification

Board CCD Camera

CCD BOARD CAMERA			
Item NO.	MS-C426	MS-C426PK	MS-C426xM
Video system.	NTSC/PAL		
Number of Effective Pixels	PAL	500x528	
	NTSC	510x492	
CCD Image Sensor	1/4" Interline CCD		
Scanning System	2:1 INTERLACE		
Synchronization	INTERNAL		
Resolution (TV Lines)	350 TV Lines		
S/N Ratio	more than 48dB		
Minimum Illumination	0.2Lux / F 1.2 (color) & 0.02Lux / F 1.2 (B/W)		
Electronic Shutter	1/50 - 1/96,000	1/50 - 1/120,000	
Horizontal Sync Frequency	NTSC(EIA)-15.73kHz / PAL(CCIR)-15.62kHz		
Vertical Sync Frequency	NTSC(EIA)-60Hz / PAL(CCIR)-50Hz		
Gamma Consumption	0.45		
Video Output	1Vp-p , 75ohms Composite		
Audio Output	Frequency 20-16000Hz,S/N ratio more than 58dB (Optional)		
Power Source	DC 5V	DC 12V	
Storage Temperature	-30 to 60 Degree C		
Working Temperature	-10 to 45 Degree C		
Power Current	150mA	120mA	150mA
Dimensions (mm)	22(W)x26(L)mm		




MS-C426PK-3C

MS-C426PK-4V

MS-C426PK-4F

MS-C426PK-xx

Holder diameter : 12mm



MS-C426PM

MS-C426GM

MS-C426xM

Holder diameter : 10mm

Ordering Information

MODEL	MICRO LENS	PIN HOLE	HOLDER DIAMETER
MS-C426G	3.6mm/F2.0		10 mm
MS-C426P		3.7mm/F2.0 (CONE)	10 mm
MS-C426GM	3.6mm/F2.0		10 mm
MS-C426PM		3.7mm/F2.0 (CONE)	10 mm
MS-C426PK-3C		4.3mm/F2.0 (CONE)	12 mm
MS-C426PK-4C		4.3mm/F2.0 (CONE)	12 mm
MS-C426PK-4V		4.3mm/F2.0 (CONE)	12 mm
MS-C426PK-4F		4.3mm/F2.0 (Flat)	12 mm

NOTE:
G : Micro Lens , P : Pin Hold Lens

Feature

High Quality picture.
Compact size.
Mirror function: ordering in advance.
Backlight compensation.
Auto white balance.
Equipping Electronics-Auto-Iris.
High performance.
Competitive price.
Exchange for any kind of lens.
High speed white balance mode (1Fild)
Outstanding Quality.

Dimensions

