

Specification

Spy CCD Camera

SPY CCD CAMERA (Wearable)	
Video system.	NTSC/PAL
Number of Effective Pixels	510X492(NTSC)
	500X582(PAL)
CCD Image Sensor	1/4" Interline CCD
Scanning System	2:1 INTERLACE
Synchronization	INTERNAL
Resolution (TV Lines)	350 TV LINE
S/N Ratio	more than 48dB
Minimum Illumination	0.2 Lux / F 1.2
Electronic Shutter	1/50 - 1/120,000
Horizontal Sync Frequency	NTSC(EIA)-15.734kHz / PAL(CCIR)-15.625kHz
Vertical Sync Frequency	NTSC(EIA)-60Hz / PAL(CCIR)-50Hz
Gamma Consumption	0.45
Video Output	1Vp-p , 75ohms Composite
Audio Output	Frequency 20-16000Hz,S/N ratio more than 63dB SPL(at 1000Hz))(Ordering in advance)
Audio Standard	Frequency 20-16000Hz,S/N ratio more than 58dB
Built-In Lens	3.7mm/F2.0
Storage Temperature	-30 to 60 Degree C
Working Temperature	-10 to 45 Degree C
Power Source	DC 7-12V(standard)
Power Current	70mA(max)



HS-11466



HS-11488



HS-121



HS-121



KS-C413



KS-C402



KS-C400



KS-C410

Wireless Kit



HVS-11488U



KS-21466UT-A2



KS-21466UT-A1

MODEL	RF Output Power	Frequency	Microphone
KS-x1466xT-A2	200mW	2.4GHz	
KS-x1466xT-A6	600mW	2.4GHz	
KS-x1466xT-B1	100mW	1.2GHz	
KS-x1466xT-B5	500mW	1.2GHz	
KS-x1466xTA-A2	200mW	2.4GHz	●
KS-x1466xTA-A6	600mW	2.4GHz	●
KS-x1466xTA-B1	100mW	1.2GHz	●
KS-x1466xTA-B5	500mW	1.2GHz	●

NOTE: KS-x1466xTA-B5

- ① ② ③④⑤⑥⑦⑧
- ⑤

① CCD KIT

② Sunglasses frame color type:

1: Shining black ; 2: Blue

③ Sunglasses frame type:

④ Sunglasses lens Color

C: Transparent Type ; B: Black Tint

Y: Yellow Tint ; U: UV Protection

R: Red ; SB: Sky blue

⑤ NEW TXT-BOX

⑥ A: W/Microphone

⑦ Transmitter & Receiver : A:2.4GHz ; B:1.2GHz

⑧ TXT-BOX RF Output Power

1: 100mW ; 2: 200mW ; 5: 500mW ; 6: 600mW

Other type



HS-11466C
(Frame Glasses)



HS-21466U
(Frame Glasses)



MRX-1200B
(NEW WIRELESS RECEIVER)



MSR-A2410B
(WIRELESS RECEIVER)

Specification

Spy CCD Camera

SPY CCD CAMERA (Wearable)	
Video system.	NTSC/PAL
Number of Effective Pixels	510X492(NTSC)
	500X582(PAL)
CCD Image Sensor	1/4" Interline CCD
Scanning System	2:1 INTERLACE
Synchronization	INTERNAL
Resolution (TV Lines)	350 TV LINE
S/N Ratio	more than 48dB
Minimum Illumination	0.2 Lux / F 1.2
Electronic Shutter	1/50 - 1/120,000
Horizontal Sync Frequency	NTSC(EIA)-15.734kHz / PAL(CCIR)-15.625kHz
Vertical Sync Frequency	NTSC(EIA)-60Hz / PAL(CCIR)-50Hz
Gamma Consumption	0.45
Video Output	1Vp-p , 75ohms Composite
Audio Output	Frequency 20-16000Hz,S/N ratio more than 63dB SPL(at 1000Hz))(Ordering in advance)
Audio Standard	Frequency 20-16000Hz,S/N ratio more than 58dB
Built-In Lens	3.7mm/F2.0
Storage Temperature	-30 to 60 Degree C
Working Temperature	-10 to 45 Degree C
Power Source	DC 7-12V(standard)
Power Current	70mA(max)



HS-11466



HS-11488



HS-121



KS-C400



KS-C413



KS-C402



KS-C410

Wireless Kit



AB22124



AB62124

MODEL	RF Output Power	Frequency	Microphone
AB22124	200mW	2.4GHz	●
AB62124	600mW	2.4GHz	●
BB12124	100mW	1.2GHz	●
BB52124	500mW	1.2GHz	●
AV22124	200mW	2.4GHz	
AV62124	600mW	2.4GHz	
BV12124	100mW	1.2GHz	
BV52124	500mW	1.2GHz	

NOTE: B B 1 2 1 2 4 :
 ① ② ③ ④ ⑤ : ① TXT-BOX : A:2.4GHz ; B:1.2GHz
 ② B: W/Microphone ; V: W/O Microphone
 ③ 1: 100mW ; 2: 200mW ; 5: 500mW ; 6: 600mW
 ④ Different appearances : 21:Button
 ⑤ 1/4" CCD M.RES

Other type



HS-C131
(SCREW)



HS-C124
(BUTTON)



MRX-1200B
(NEW WIRELESS RECEIVER)



MSR-A2410B
(WIRELESS RECEIVER)