


**Feature**

- Hi Resolution up to 400 TV Lines.
- Compact size.
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality!
- Competitive Price!
- Substitution for door "peepholes"



Unit : mm (±0.5)

**Specification**

|                            |                                   |
|----------------------------|-----------------------------------|
| Model                      | MF-35D                            |
| Video system               | NTSC / PAL                        |
| Number of effective pixels | 648 x 480 (NTSC & PAL)            |
| Image sensor               | 1/4" Color CCIQ II Camera         |
| Resolution(TV Lines)       | 400 TV Lines                      |
| S/N Ratio                  | more than 50dB                    |
| Minimum illumination       | 0.1 LUX / F1.2                    |
| Image Transfer Rate        | 60 fps.                           |
| Horizontal sync frequency  | NTSC -15.734kHz , PAL - 15.625kHz |
| Vertical sync frequency    | NTSC - 60Hz , PAL - 50Hz          |
| Camera consumption         | 0.45                              |
| Video output               | 1Vp-p , 75ohm composite           |
| Storage temperature        | -30 to 60 Degree C                |
| Working temperature        | -10 to 45 Degree C                |
| Built-in Lens              | 1.8 mm/F2.5                       |
| Power source               | DC 5~12 V(Standard)               |
| Power current              | 50 mA                             |





▲ MF-35D

**Ordering information**

**MF-35D**

Door Peephole Camera



**Other information**


**MF-35D-3D**

NEW CCIQ II Camera



**Feature**

- Hi Resolution up to 400 TV Lines.
- Compact size.
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality!
- Competitive Price!
- Substitution for door "peepholes"



Unit : mm (±0.5)

**Specification**

|                            |                                   |
|----------------------------|-----------------------------------|
| Model                      | MF-35D-3D                         |
| Video system               | NTSC / PAL                        |
| Number of effective pixels | 648 x 480 (NTSC & PAL)            |
| Image sensor               | 1/4" Color CCIQ II Camera         |
| Resolution(TV Lines)       | 400 TV Lines                      |
| S/N Ratio                  | more than 50dB                    |
| Minimum illumination       | 0.1 LUX / F1.2                    |
| Image Transfer Rate        | 60 fps.                           |
| Horizontal sync frequency  | NTSC -15.734kHz , PAL - 15.625kHz |
| Vertical sync frequency    | NTSC - 60Hz , PAL - 50Hz          |
| Camera consumption         | 0.45                              |
| Video output               | 1Vp-p , 75ohm composite           |
| Storage temperature        | -30 to 60 Degree C                |
| Working temperature        | -10 to 45 Degree C                |
| Built-in Lens              | 3.9 mm/F2.8                       |
| Power source               | DC 5~12 V(Standard)               |
| Power current              | 50 mA                             |





▲ MF-35D-3D

**Ordering information**

**MF-35D-3D**

Door Peephole Camera



**Other information**

**MF-35D**

NEW CCIQ II Multi-Function Camera  
 Waterproof IP 68

