


Feature

- Hi Resolution up to 400 TV Lines.
- Compact size.
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality!
- Competitive Price!
- Substitution for door "peepholes"



Unit : mm (±0.5)

Specification

Model	MF-35D
Video system	NTSC / PAL
Number of effective pixels	648 x 480 (NTSC & PAL)
Image sensor	1/4" Color CCIQ II Camera
Resolution(TV Lines)	400 TV Lines
S/N Ratio	more than 50dB
Minimum illumination	0.1 LUX / F1.2
Image Transfer Rate	60 fps.
Horizontal sync frequency	NTSC -15.734kHz , PAL - 15.625kHz
Vertical sync frequency	NTSC - 60Hz , PAL - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Built-in Lens	1.8 mm/F2.5
Power source	DC 5~12 V(Standard)
Power current	50 mA





▲ MF-35D

Ordering information

MF-35D

Door Peephole Camera



Other information


MF-35D-3D

NEW CCIQ II Camera



Feature

- Hi Resolution up to 400 TV Lines.
- Compact size.
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality!
- Competitive Price!
- Substitution for door "peepholes"



Unit : mm (±0.5)

Specification

Model	MF-35D-3D
Video system	NTSC / PAL
Number of effective pixels	648 x 480 (NTSC & PAL)
Image sensor	1/4" Color CCIQ II Camera
Resolution(TV Lines)	400 TV Lines
S/N Ratio	more than 50dB
Minimum illumination	0.1 LUX / F1.2
Image Transfer Rate	60 fps.
Horizontal sync frequency	NTSC -15.734kHz , PAL - 15.625kHz
Vertical sync frequency	NTSC - 60Hz , PAL - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Built-in Lens	3.9 mm/F2.8
Power source	DC 5~12 V(Standard)
Power current	50 mA





▲ MF-35D-3D

Ordering information

MF-35D-3D

Door Peephole Camera



Other information

MF-35D

NEW CCIQ II Multi-Function Camera
 Waterproof IP 68

