



**Feature**

- Hi Resolution up to 380 TV Lines.
- Compact size.
- Ultra-lightweight!
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality!
- Day & Night Lens

**Specification**

Unit : mm (± 0.5)

Model	MO-B2626-4F
Video system	NTSC / PAL
Number of effective pixels	510 x 492-NTSC , 628 x 582-PAL
Image sensor	1/3" CCIQ Color Camera
Resolution(TV Lines)	380 TV Lines
S/N Ratio	more than 48dB
Minimum illumination	0.2 LUX / F1.2
Shutter Speed	1/50-1/125.000 sec
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Built-in Lens	4.3 mm/F2.0
Power source	DC 5~12 V(Standard)
Power current	50 mA(DC 12V)
Dimension (mm)	22 x 26 (mm)



MO-B2626-4F

**Ordering Information**

MODEL	LENS	MIC.	TYPE	MODEL	LENS	MIC.	TYPE
MO-B2626-3C	3.7mm / F2.0	x	CONE	MO-B2626YA-3C	3.7mm / F2.0 Day & Night Lens	Built-in	CONE
MO-B2626-4C	4.3mm / F2.0	x	CONE	MO-B2626YA-4C	4.3mm / F2.0 Day & Night Lens	Built-in	CONE
MO-B2626-3F	3.7mm / F2.0	x	FLAT	MO-B2626YA-3F	3.7mm / F2.0 Day & Night Lens	Built-in	FLAT
MO-B2626-4F	4.3mm / F2.0	x	FLAT	MO-B2626YA-4F	4.3mm / F2.0 Day & Night Lens	Built-in	FLAT
MO-B2626-3T	3.1mm / F3.4	x	SLIM	MO-B2626YA-3T	3.1mm / F3.4 Day & Night Lens	Built-in	SLIM
MO-B2626-4T	3.9mm / F3.9	x	SLIM	MO-B2626YA-4T	3.9mm / F3.9 Day & Night Lens	Built-in	SLIM
MO-B2626G	3.6mm / F2.0	x	G-TYPE	MO-B2626GYA	3.6mm / F2.0 Day & Night Lens	Built-in	G-TYPE

**Note:**

MO-B2626GYA A : External Mic. MO-B2626GYA Y : Day & Night Lens

**Other information**

**N-1426G**

1/4" Color CCD Camera



**MO-N3531**

1/4" Color CCIQ II Hidden Camera

