



Unit : mm (±0.5)

Feature

- NEW CCIQ II Sun Glasses Camera
- Hi Resolution Up To 400 TV Lines.
- Wearable Hidden Video Glasses
- Excellent Concealment
- Backlight Compensation.
- High Quality Picture.

Specification

Model	MO-N3588U-3T
Video system	NTSC & PAL
Number of effective pixels	648 x 488 (NTSC & PAL)
Image sensor	1/4" Color CCIQ II Camera
Resolution(TV Lines)	400 TV Lines
S/N Ratio	more than 50dB
Minimum illumination	0.1 LUX / F1.2
Image Transfer Rate	60 field/sec (NTSC) , 50 field/sec (PAL)
Horizontal sync frequency	(NTSC)- 15.734kHz , (PAL)- 15.625kHz
Vertical sync frequency	(NTSC) - 60Hz , (PAL) - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Audio output	20-16000Hz,S/N more than 58dB (Optional)
Built- in Lens	3.4mm / F3.4(3T) , 4.3mm / F2.0(4T)
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Power source	DC 5~12V (Standard)
Power current	50 mA



▲ MO-N3588U-3T

Ordering Information

MODEL	CAMERA LENS	LENSES	MIC.	MODEL	CAMERA LENS	LENSES	MIC.
MO-N3588U-3T	3.4mm / F3.4	UV Protection	x	MO-N3588UA-3T	3.4mm / F3.4	UV Protection	External
MO-N3588C-3T	3.4mm / F3.4	Transparent Type	x	MO-N3588CA-3T	3.4mm / F3.4	Transparent Type	External
MO-N3588B-3T	3.4mm / F3.4	Black Tint	x	MO-N3588BA-3T	3.4mm / F3.4	Black Tint	External
MO-N3588U-4T	3.9mm / F3.9	UV Protection	x	MO-N3588UA-4T	3.9mm / F3.9	UV Protection	External
MO-N3588C-4T	3.9mm / F3.9	Transparent Type	x	MO-N3588CA-4T	3.9mm / F3.9	Transparent Type	External
MO-N3588B-4T	3.9mm / F3.9	Black Tint	x	MO-N3588BA-4T	3.9mm / F3.9	Black Tint	External

Note:

MO-N3588U: 1/4" Color CCIQ II Camera

Other information

