



Body Type


3C Lens




3F Lens




3T Lens




4C Lens



4F Lens



4T Lens



Unit : mm (± 0.5)

Feature

- Compact size.
- Hi Resolution up to 400 TV Lines.
- High Performance.
- Outstanding Quality!
- Competitive Price!

Specification

Model	MO-S3510	MO-S3710
Video system	NTSC / PAL	EIA / CCIR
Number of effective pixels	648 x 480	
Image sensor	1/4" CCIQ II Color Camera	1/4" CCIQ II B/W Camera
Resolution(TV Lines)	400 TV Lines	
S/N Ratio	more than 50dB	
Minimum illumination	0.1 LUX / F1.2	
Electronic shutter	60 field/sec (NTSC) ,50 field/sec (PAL)	
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz	
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz	
Camera consumption	0.45	
Video output	1Vp-p , 75ohm composite	
Audio output	Frequency 20-16000Hz,S/N ratio more than 58dB SPL (Ordering in advance)	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Power source	Camera :DC 5~12V	
Power current	60 mA-max (DC 12V)	
Dimension (mm)	11 x 11 (mm)	



MO-S3510-3C



MO-S3510-4C



MO-S3510-3F



MO-S3510-4F



MO-S3510-3T



MO-S3510-4T

Ordering Information

Model	Lens	Mic.	Model	Lens	Mic.
MO-S3510-3C	3.7mm / F2.0	x	MO-S3510A-3C	3.7mm / F2.0	External
MO-S3510-4C	4.3mm / F2.0	x	MO-S3510A-4C	4.3mm / F2.0	External
MO-S3510-3F	3.7mm / F2.0	x	MO-S3510A-3F	3.7mm / F2.0	External
MO-S3510-4F	4.3mm / F2.0	x	MO-S3510A-4F	4.3mm / F2.0	External
MO-S3510-3T	3.1mm / F3.4	x	MO-S3510A-3T	3.1mm / F3.4	External
MO-S3510-4T	3.9mm / F3.9	x	MO-S3510A-4T	3.9mm / F3.9	External

Note:

- MO-S3510A-xx A : External Mic.
- MO-S3510A-xx 1/4" CCIQ II Color Camera

Other information

MO-N3531

1/4" Color CCIQ II Camera

