



Body Type


2S Lens




3S Lens



2V Lens



3V Lens



Unit : mm (± 0.5)

Feature

- Super Wide-angle
- Compact size.
- Hi Resolution up to 400 TV Lines.
- High Performance.
- Outstanding Quality!
- Competitive Price!

Specification

Model	MO-S58
Video system	NTSC / PAL
Number of effective pixels	648 x 480
Image sensor	1/4" CCIQ II Color Camera
Resolution(TV Lines)	400 TV Lines
S/N Ratio	more than 50dB
Minimum illumination	0.6 LUX / F1.2
Electronic shutter	60 fps.
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Audio output	Frequency 20-16000Hz,S/N ratio more than 58dB SPL (Ordering in advance)
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Power source	Camera :DC 5~12V
Power current	50 mA-max (DC 12V)
Dimension (mm)	8.5 x 8.5 (mm)



▲ MO-S58

Ordering Information

MODEL	FOCUS LENS	MIC.	LENS THREAD
MO-S58A-2S	2.1mm / F2.5	External	M 5.5 mm, P0.35mm
MO-S58A-3S	3.4mm / F3.4	External	M 5.5 mm, P0.35mm
MO-S58A-2V	2.95mm / F3.2	External	M 7 mm, P0.5mm
MO-S58A-3V	3.3mm / F2.0	External	M 7 mm, P0.5mm
MO-S58A-4F	4.0mm / F2.0	External	M 7 mm, P0.5mm
MO-S58-2S	2.1mm / F2.5	W/O MIC.	M 5.5 mm, P0.35mm
MO-S58-3S	3.4mm / F3.4	W/O MIC.	M 5.5 mm, P0.35mm
MO-S58-2V	2.95mm / F3.2	W/O MIC.	M 7 mm, P0.5mm
MO-S58-3V	3.3mm / F2.0	W/O MIC.	M 7 mm, P0.5mm
MO-S58-4F	4.0mm / F2.0	W/O MIC.	M 7 mm, P0.5mm

NOTE

Cable length : ordering in advance

MO-S58A: A: External Mic.