



Body Type


2S Lens




3S Lens



2V Lens



3V Lens




Unit : mm (± 0.5)

Feature ■

- Super Wide-angle
- Compact size.
- Hi Resolution up to 400 TV Lines.
- High Performance.
- Outstanding Quality!
- Competitive Price!

Specification

Model	MO-S2588	MO-S2788
Video system	NTSC / PAL	EIA / CCIR
Number of effective pixels	648 x 480	
Image sensor	1/4" CCIQ II Color Camera	1/4" CCIQ II B/W Camera
Resolution(TV Lines)	400 TV Lines	
S/N Ratio	more than 50dB	
Minimum illumination	0.6 LUX / F1.2	
Electronic shutter	60 fps.	
Horizontal sync frequency	NTSC(EIA) - 15.734kHz , PAL(CCIR) - 15.625kHz	
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz	
Camera consumption	0.45	
Video output	1Vp-p , 75ohm composite	
Audio output	Frequency 20-16000Hz,S/N ratio more than 58dB SPL (Ordering in advance)	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Power source	Camera :DC 5~12V	
Power current	50 mA-max (DC 12V)	
Dimension (mm)	8.6mm x 8.6mm +protection tape	



▲ MO-S2588

Ordering Information

MODEL	FOCUS LENS	MIC.	LENS THREAD
MO-S2588A-2S	2.1mm / F2.5	External	M 5.5 mm, P0.35mm
MO-S2588A-3S	3.1mm / F3.4	External	M 5.5 mm, P0.35mm
MO-S2588A-2V	2.8mm / F3.9	External	M 7 mm, P0.5mm
MO-S2588A-3V	3.3mm / F2.0	External	M 7 mm, P0.5mm
MO-S2588-2S	2.1mm / F2.5	X	M 5.5 mm, P0.35mm
MO-S2588-3S	3.1mm / F3.4	X	M 5.5 mm, P0.35mm
MO-S2588-2V	2.8mm / F3.9	X	M 7 mm, P0.5mm
MO-S2588-3V	3.3mm / F2.0	X	M 7 mm, P0.5mm

NOTE

Cable length : ordering in advance
 MO-T2588: 1/4" Color CCIQ II
 MO-T2788: 1/4" B/W CCIQ II
 MO-T2588A: External Mic.