



EDD-TL20942L


Unit : mm (± 0.5)



EDD-SL20959L-76



EDD-SL20959L-128



Feature

- High Sensitivity!
- High Performance.
- UVC Rigid Camera
- Ø 5.9 mm only
- 1280x720 resolution
- Light source adjustable

Specification

Model	EDD-TL20942L	EDD-SL20959L
		Color
Dimension(mm)	Ø4.2	Ø5.9
Max. frame rate	1280x720@ 30fps MJPG/ 10fps YUV	
Pixel size	1.4 µm x 1.4 µm	
Image sensor	1/9" Digital CMOS Camera Module	
Image area	1.819 x1.033 mm	
Scan mode	progressive	
Sensitivity	585mV/Lux-sec	
Dynamic range	68.4dB @16x gain	
UVC format	MJPEG, YUY2	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Interface	USB 2.0 (Compliant with USB Video Class 1.1 standard)	
Shutter	rolling shutter	
Operating system	Windows XP, Windows Vista, Window 7, Windows 8	
Power source	DC 5V (USB/with power board)	
Power current	170mA	

More Information

EDD-	SL-	209	59	L	-76
EDD: USB A	SL: Side view	sensor	42: Ø4.2mm	L: white LED	76: 76° lens
EDM: Micro USB	TL: Front view		59: Ø5.9mm	L8: IR 850nm LED	128: 128° lens
EDT: USB C				L9: IR 940nm LED	
			tube diameter's size can be customized SL: Side view Ø5.9mm TL: Front view Ø4.2mm	LED power switch	

