


**Feature**

- High Sensitivity!
- High Performance & Super low light.
- Spy camera + IR LED
- 550 TV lines
- Compact size

**Specification**

unit : mm (±0.5)

Model	MX-S5517KU	MX-S9531KU	MX-S9581KU	MX-S5717KU	MX-S9731KU	MX-S9781KU
Video system	NTSC / PAL			EIA / CCIR		
Number of effective pixels	720 x 480 ( NTSC/EIA & PAL/CCIR )					
Image sensor	4.86mm(1/3.7") CCIQIII color			4.86mm(1/3.7") CCIQIII B/W		
Resolution(TV Lines)	480 TV Lines			550 TV Lines		
S/N Ratio	47 [dB]					
Max Dynamic Range	63.3 [dB]					
Sensor scan mode	progressive scan					
Minimum illumination	0.03 Lux / 50IRE, 15 fps-LED turn off / 60cm 0.03 Lux / 140IRE, 15 fps-LED turn on / 60cm					
LED	N/A	IR 940 nm LED x 12		N/A	IR 940 nm LED x 12	
Sensitivity	8.2[V/Lux.sec]					
Frame Rate	15 fps					
Horizontal sync frequency	NTSC/EIA - 15.734kHz , PAL/CCIR - 15.625kHz					
Vertical sync frequency	NTSC/EIA - 60Hz , PAL/CCIR - 50Hz					
Gamma consumption	0.45					
Video output	1Vp-p , 75ohm composite					
Storage temperature	-30 to 60 Degree C					
Working temperature	-10 to 45 Degree C					
Power source	Camera input: DC 5-12V					
Power current	160 mA(max)-DC12V					
Dimension (mm)	17.5 x 22 mm					



**Ordering information**

Lens	Lens specification	View angle	Thread pitch
2V	2.8mm/ F3.9	H= 25° 22'; V= 14° 21'; D= 28° 50'	M7 x P0.5
3T	3.4mm/F3.4	H= 22° 59'; V= 12° 58'; D= 26° 9'	M7 x P0.5
3M	3.4mm/F2.8	H= 20° 60'; V= 11° 50'; D= 23° 55'	M6 x P0.35
3D	3.9mm/F2.8	H= 18° 21'; V= 10° 20'; D= 20° 55'	M7 x P0.35
• 4F	4.0mm/F2.0	H= 17° 54'; V= 10° 4'; D= 20° 24'	M7 x P0.5
• 6F	6.38mm/F4.4	H= 11° 17'; V= 6° 19'; D= 12° 53'	M7 x P0.5

Note

- For spy application
- IR LED 940nm , IR LED 850nm, white LED- ordering in advance